

Moyno Progressing Cavity Pump

Mfg: Moyno

Model: 2FG3SSQAAA

Stock No: SPPP1500

Serial No: AS-68193

Moyno Progressing Cavity Pump. Model: 2FG3SSQAAA. Capacity: 3.5 gpm @ 130 psi. Frame: SSQ. Form: FF. Dayton Motor Drive, 1-1/2 hp, 1740 rpm, 669 rpm (final), 230/460 V, 4.8/2.4 amps, 60 Hz, 3 phase. Materials of construction: 304 stainless steel casing, 316 stainless steel internal components, and Nitrile stator. FF series pumps are designed for use where the material being pumped is relatively free flowing. The suction and discharge ports are equipped with easy cleaning threaded connections. Screw dimensions: 1 ft. L x 1-1/2 in. diameter. Inlets/outlets: (2) 1-1/2 in. dia. threaded fittings. Overall dimensions: 3 ft. 1 in. L x 1 ft. 1 in. W x 2 ft. 5 in. H.





