

Greon Gas-Fired Steam Jacketed Kettle - 40 Gallon

Mfg: Groen

Model: AH/1-40

Stock No: SPPP617.3a

Serial No: 130D

Greon Gas-Fired Steam Jacketed Kettle - 40 Gallon. Model: AH/1-40. S/N: 130D. Nat'l Bd: 69075. Gas-fired: natural or propane. MAWP @ 300 °F: 45 psi. Input rate: 100,000 Btuh. Open top with lift-top lid. Natural gas feed rate (min/max): 4.5/14 in. W.C. Features include: 180 emery grit finished interior, thermostatically controlled shut off. Great for chain restaurants, supermarkets, schools, and healthcare facilities. Electrical requirements: 115 V, 1 amp, 60 Hz, single phase. Inlets: (1) 3/4 in. dia. NPT (male, jacket), (1) 3/4 in. dia. NPT (male, natural gas), (1) 4 in. dia. pilot access door. Outlets: (1) 3/4 in. dia. NPT (female, jacket), (1) 1-1/2 in. dia. discharge, (1) 6 in. dia. exhaust port. Overall dimensions: 40 in. L x 38 in. W x 43 in. H.

