

Groen Capkold Bottom-Jacketed Cook Tank

Mfg: Groen

Model: CookTank

Stock No. SPPP983.20a

Serial No. 128891

Groen Capkold Bottom-Jacketed Cook Tank. Model: CookTank. S/N: 128891. Stainless steel. MAWP 100 psi @ 338 °F. Inside dimensions: 63 in. L x 32 in. W x 34 in. H. (4) 58-1/2 in. L x 24 in. W x 5 in. H wire baskets with (5) 24 in. L x 11 in. W x 5 in. H sections. High performance water circulating pump and rear mounted, water-cooled heat exchanger. Strut-assisted top. Prepiped connections. Lifting rack for easy hoist removal. Inlets: (1) 3/4 in. dia. port (cooking media), (1) 3/4 in. dia. NPT (female, jacket), (1) 1-1/2 in. dia. port (cooking media level indicator), (1) 2 in. dia. bevel fitting with hex (heat exchanger water), (1) 3 in. dia. port (cooking media circulation). Outlets: (1) 3/4 in. dia. NPT (female, jacket), (1) 1-1/2 in. dia. port (tank discharge), (1) 2 in. dia. NPT (male, heat exchanger water), (2) 2 in. dia. ports (cooking media circulation). Overall dimensions: 88 in. L x 47 in. W x 49 in. H. ACN840

Ametek Water-Cooled Shell and Tube Heat Exchanger, Model: MHT-2-B-CB, S/N: WL-42371/1, size: 6 in. dia. x24 in. L, shell side MAWP @ 300 °F: 210 psig, tube side MAWP @ 300 °F: 200 psig. Tri Clover C218 Centrifugal Pump, Model: C218MD18T-S, S/N: U0108. Reliance Electric Motor, 3 hp, 1730 rpm, 230/460 V, 9.2/4.6 amps, 60 Hz, 3 phase. Hubbel level indicator.





