

Shriver Plate and Frame Filter Press

Mfg: Shriver

Model:

Stock No. 45.SS3a.5

Serial No. 28594

Shriver Plate and Frame Filter Press. S/N 28594. (25) Cast steel plates. Plate dimensions: 12 in. L x 1 in. W. x 12 in. H. Cake capacity: 25 sq. ft. Filter pressure with Shriver Diaphragm Pump, size 0E8, S/N G475. Induction Motor, 1.5 hp, 1730 rpm. 230/460 V, 4.8/2.4 amps, 60 Hz, 3 phase. Inlets/outlets: 2-1/2 dia. ports. Overall Dimensions: 44 in. L x 26 in. W x 40 in. H.



