

Schmidt-Bretten Plate Heat Exchanger – 938 Sq. Ft.

Mfg: Schmidt-Bretten


Model: 37-150

Stock No: SSFF1019.32a

Serial No: 26093 HX

Schmidt-Bretton Plate Heat Exchanger. Model: 37-150. S/N: 26093 HX. (250) 316 stainless steel plates. Total heat transfer surface area: 938.3 sq. ft. Heat transfer surface area per plate: 11-1/2 in. W x 3 ft. 11 in. H. Plate overall dimensions: 1 ft. 2 in. W x 4 ft. 1/2 in. H. M.A.W.P: 150 PSIG. Test Press. 225 PSIG. Design Temp. 250 °F. Minimum tightening dimension between covers with 250 plates: 45.4 in. Inlets/outlets: (6) 3 in. S-line. Overall dimensions: 8 ft. 9 in. L x 2 ft. 2 in. W x 5 ft. 10-1/2 in. H.





Schmidt
PLATE HEAT EXCHANGER

MODEL NO.	SIGMA 37-150	CUSTOMER	
SERIAL NO.	26093 HX	EQT. NO.	
M.A.W.P.	150 PSIG		
TEST PRESS.	225 PSIG		
DESIGN TEMP.	250 °F		

MATERIAL : PLATE 316 SS GASKET NITRIL
MINIMUM TIGHTENING DIMENSION BETWEEN COVERS WITH 250 PLATES : 75.700 INCHES
SCHMIDT-BRETEN, INC - DETROIT, MICHIGAN - (313) 863 0150

