

## 1990 G.J. Olney Flotation Washer

Mfg: G.J. Olney

Model:

Stock No. SSLP182.5a

Serial No. 926 G 70

1990 G.J. Olney Flotation Washer. S/N: 926 G 70. Motor: 7.5 hp, 1165 rpm, 460 V, 10 amps, 60 Hz, 3 phase. Deming pump, 10 in. diameter flange with (8) holes, center to center: 9 in. Three stages: 1st Washer/Divider, 2nd Flotation/Divider, 3rd Exit/Divider. Washer/Divider platform: 92 in. L x 60 in. W x 5 in. H. (14) Sections: 4-1/2 in. W x 32 in. L. Flotation/Divider: 60 in. L x 26 in. W. Exit height: 47 in. H. Recirculation water system. Water inlet: 3/4 in. pipe. Outlets: 1st stage: (2) in. threaded female, 3rd stage: (3) 2-1/2 in. threaded female. Overall dimensions: 98 in. L x 87 in. W x 71 in. H.



