

Vanmark Peeler/Scrubber/Washer Machine

Mfg: Vanmark



Model: 26


Stock No: SSLP656.31

Serial No:



Vanmark Peeler/Scrubber/Washer Machine. Model: 26. Stainless steel body. Spray bar dimensions: 5 ft. 8-1/2 in. L x 1/2 in. W with 9 holes. Open/close doors (manual) on both sides. Feeder dimensions: 11-3/4 in. W x 1 ft. 3 in. H. Water inlet: 1 in. threaded female. This machine is for peeling, washing, and/or scrubbing root crops, vegetables, or fruits. Baldor motor, 10 hp, 1760 rpm, 208-230/460 V, 27.5-25.6/12.8 amps, 60 Hz, 3 phase. Pulley drive ratio: 3.0. Final rpm: 586. Overall dimensions: 9 ft. 9 in. L x 2 ft. 11-1/2 in. W x 4 ft. 7 in. H. (ACN500)











BALDOR
WASHDOWN DUTY MOTOR

BALDOR ELECTRIC CO. FT. SMITH, AR, MFG. IN U.S.A.

CAT. NO.	WDM3714T		
SPEC.	37H872T977H1		
HP	10		
VOLTS	208-230/460		
AMPS	27.5-25.6/12.8		
R.P.M.	1760		
FRAME	215T	HZ 60	PH 3
SER. F.	1.15	CODE U	DES B CLASS F
NEHA NOM. EFF.	89.5	% P.F.	B1
STATING	40C AMB-CONT		
CC	D10A	USABLE AT 208V	A
WEIGHTS	DE 6307	LOC 6206	
ENCL.	TEFC	SH F0701031265	

