

Vanmark Peeler/Scrubber/Washer Machine


Mfg: Vanmark


Model: 2600

Stock No. SSLP656.31

Serial No.

Vanmark Peeler/Scrubber/Washer Machine. Series 2600. Stainless steel body. Spray bar dimensions: 68-1/2 in. L x 1/2 in. W with 9 holes. Does not have rolls. Open/close doors (manual) on both sides. Feeder dimensions: 11-3/4 in. W x 15 in. H. Water inlet: 1 in. threaded female. This machine is for peeling, washing, and/or scrubbing root crops, vegetables, or fruits. Overall dimensions: 9 ft. 9 in. L x 35-1/2 in. W x 55 in. H.





VANMARK PEELER/SCRUBBER/WASHER.

The Series 2600 Peeler/Scrubber/Washer is designed for use where the capacity and versatility of a full-size continuous unit is needed, but where the duty cycle does not justify a larger investment. It will peel, scrub, or wash thousands of pounds of carrots, potatoes, onions, beets, apples or other products per day. Product enters the machine via the inlet chute. Surface debris or peel is then removed by six or eight rolls which contact and tumble the product until it exits the machine. A wide selection of roll surfaces is available. The amount of material removed is fully controllable using a combination of gate position and roll speed settings. Vanmark specialists will help configure the roll arrangement to suit your application. Available options include a tumbling unit, drain pan, and reversing roll. The Series 2600 Peeler/Scrubber/Washer is built to give many years of dependable service.