

Stainless Steel 2-Head Pneumatic Piston Filler- 23 cu. in.

Mfg:	Model:
Stock No. SSLP898.7	Serial No.:

Stainless Steel 2-Head Pneumatic Piston Filler- 23 cu. in. Infeed hopper diameter: 28 in. Piston diameter and stroke: 2 in. dia. x 5 in. L. Pneumatic piston activates discharge. Electrical requirements: 220 V, 10 amps. (4) Casters allow for easy positioning. Inlets: (1) 3 in. dia. infeed. Outlets: (2) 1 in. dia. discharge ports. Overall dimensions: 55 in. L x 30 in. W x 69 in. H.

