

## Mycom N62WB Compound Reciprocating Compressor - 100 HP

Mfg: Mycom

Model: N62WB

Stock No: STTW041.19

Serial No: 840029

Mycom Reciprocating Compressor. Model: N62WB. Serial: 840029. Leak (PSIG) HP: 313, LP: 185. Hyd (PSIG) HP: 470, LP: 470. Mayekawa Mfg. Co. Ltd. Made in Japan. Refrigerant: ammonia (R-717 / NH4). Rated capacity: 66 tons at 110 hp (95F condensing / -4F evaporator). (8) cylinders: (6) low stage and (2) high stage. Bore: 5-1/8. Stroke: 3-15/16. Rated compressor maximum speed: 1200 rpm. Maximum speed displacement: low stage 337 cfm and high stage 112 cfm. Capacity control steps (%): 100, 66, 33. Lincoln Lincguard motor: 100 HP, 1770 rpm, 230/460V, 238/119 amps, 60 Hz, 3 phase. \*Note: unit has a crack in the body, see the pdf pictures file. Estimated weight: 5,200 lbs. Overall dimensions: 7 ft. 11 in. L x 4 ft. 5 in. W x 5 ft. H.





