

FES Rotary Screw Compressors- 300 HP

Mfg: FES

Model: 225-LE

Stock No. TAAR001.

Serial No. 2030150 and 2030139

(2) FES Rotary Screw Compressors- 300 HP. Model: 225- LE. S/N's: 2030139 and 2030150 (Mycom Model VMD 200). Refrigerant: R-22. Leak test pressure: 313 psi. Hydrostatic test pressure: 470 psi. Price for the VMD 200 bare compressor, is \$24,450. Technical details for a Model VMD 200: displacement- 718 CPM, capacity: 262.6 TR (R-717), power: 280 BHP (R-717), capacity: 172.3 TR (R-22), power: 293.9 BHP (R-22). Toshiba High Efficiency Induction Motor, 300 hp, 3540 rpm, 460 V, 330 amps, 60 Hz, 3 phase. Inlets/outlets: (2) 6 in. dia. flanged ports (refrigerant suction/discharge). Overall dimensions: 7 ft. 3-1/2 in. L x 2 ft. 9 in. W x 2 ft. H.



