

### Tri-Clover PRE300 Positive Displacement Pump

**Mfg: Tri-Clover**

**Model: PRE300-4M-UH4-SL-S**

**Stock No: TACJ0212.22a**

**Serial No: T0136**

Tri-Clover Positive Displacement Pump. Model: PRE300-4M-UH4-SL-S. S/N: T0136. Flow rate for new pump is 300 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. (2) 7-3/4 in. rotors. Sterling Electric motor: 10 Hp, 1755 RPM, 230/460 V, 26.4/13.2 A, 60 Hz, 3 Phase. Sterling Electric drive: 10 output Hp, 1755/850 RPM in/out, 3.37 gear ratio. Inlet/outlet: (2) 4 in. S-Line. Overall dimensions: 5 ft. 2 in. L x 1 ft. 6-1/2 in. W x 2 ft. 4-5/8 in. H.





