

Kelley Incinerator

Mfg: Kelley

Model:

Stock No: TACJ0773A.a

Serial No:

Kelley Incinerator. ASCO® valve: Cat no. 8030A16. Allen Bradley reset timer: 100/120 V, 6 watts, 50/60 Hz. Dayton motor: 1/3 Hp, 3450 Rpm, 115 V, 6.6 A, 60 Hz, 1 Phase. Inside door dia: 4 ft. 4 in. Inlets/outlets: (1) 1 ft. 2 in. flange dia. with (12) 1/2 in. mounting holes. 5-3/8 in. adjacent, 21-1/8 in. opposite. (2) 3 in. ports. (1) 3/4 in. FNPT, air/water 1/2 in. pipe. Overall dimensions: 6 ft. 7 in. L x 6 ft. W x 11 ft. 6-3/4 in. H.







