

## Hosokawa Bepex Rietz® Disintegrator

**Mfg: Hosokawa Bepex Rietz®**

**Model: RD-18-H32**

**Stock No: TGP515a.32**

**Serial No: RD-661080**

Hosokawa Bepex Rietz® Disintegrator. Model: RD-18-H32. S/N: RD-661080. Rotor Diameter: 18 in. (24) cutting blades. Cast Iron construction. Hammer dimensions: 4 in. L x 2 in. W. (2) 1 ft. 10 in. W x 1 ft. 7-1/4 in. H side access doors. Motor manufacturer: U.S. Electrical Motors 75 hp, 1775 rpm, 230/460 volts, 175/88 amps, 60 Hz, 3 phase. Inlets: (1) 2 in. acme, (1) 11-1/2 in. W x 11 in. H U-shaped feed. Outlets: (1) 18 in. dia. pulp discharge, (1) 32 in. dia. liquid discharge. Motor overall dimensions: 2 ft. 1 in. L x 2 ft. W x 3 ft. 5 in. H. Rietz® disintegrator / mills give outstanding performance in the following process functions: dry pulverizing to coarse or fine grinds, wet grinding to produce slurries or pastes, shredding of difficult-to-grind materials that are high in moisture and / or oil, and fine pulping of soft fruits and vegetables. Overall dimensions: 3 ft. 9 in. L. x 3 ft. 4-1/8 in. W. x 7 ft. 3-1/2 in.





