

Bell & Gossett 1510 Series Centrifugal Pump

Mfg: Bell & Gossett

Model: 4BC

Stock No: THHS005

Serial No:2095824

Bell & Gossett 1510 Series Centrifugal Pump. Model: 4BC. S/N: 2095824. Capacity: 786 gpm @ 6.5 TDH. MAWP: 175 psi. (1) 9-1/2 in. dia. impeller. Uses: Hydronic heating and cooling systems, general service and industrial. Lincoln Electric Motor, 20 hp, 1750 rpm, 200/400 V, 57.0/28.5 amps, 60 Hz, 3 phase. Inlets: (1) 10-1/4 in. flange with (8) 3/4 in. bolt holes and (1) 5 in. suction port. Outlets: (1) 9 in. flange with (8) 1/2 in. bolt holes and (1) 4 in. discharge port. Overall dimensions: 3 ft. 10 in. L x 1 ft. 9-1/2 in. W x 1 ft. 10-1/4 in. H.



