

## Bell & Gossett 1510 Series Centrifugal Pump

Mfg: Bell & Gossett

Model: 4AC 70 BF

Stock No. THHS013.

Serial No. \_\_\_\_\_

Bell & Gossett 1510 Series Centrifugal Pump. Model: 4AC 70 BF. Capacity: 624 gpm. Lincoln Electric Motor, 7.5 hp, 1745 rpm, 200/400 V, 23.5/11.8 amps, 60 Hz, 3 phase. Inlets: 5 in. dia. suction port with an 11 in. flange. Outlets: (1) 4 in. dia. discharge port with a 9-1/2 in. dia. flange. Overall dimensions: 36-1/2 in. L x 19 in. W x 18-1/2 in. H.

