

Stainless Steel Pressure Vessel

Mfg:

Model:

Stock No: TMCB385.1

Serial No:

Stainless Steel Pressure Vessel. Inlets/outlets: (2) 4 in. ports. (1) 2 in. S-line. (1) 1-1/2 in. port. Inside vessel dimensions: 1 ft. 6 in. dia. x 1 ft. 11-1/8 in. straight wall. Perforated basket dimensions: 1 ft. 1-3/8 in. dia. x 1 ft. 4 in. H. Overall dimensions: 2 ft. 1 in. L x 1 ft. 10 in. W x 4 ft. 6 in. H.





