

APV Stainless Steel Jacketed Processor Tank-800 Gallons

Mfg: APV

Model:

Stock No. UGHB008.

Serial No.:

APV Stainless Steel Jacketed Processor Tank-800 Gallons. Inside straight wall dimensions: 6 ft. dia. x 6 ft. 2 in. H. MAWP: 75 psig @ 350°F. Reliance Electric Motor, 2 hp, 1740 rpm, 460 V, 2.9 amps, 3 phase. Reliance Gearmotor, ratio: 121, rpm out: 14 (final). Maximum number of scrapers: 6. Scraper dimensions: 3-1/2 in. W x 10-1/2 in. L. Blade dimensions: 5-1/2 in. W x 5 ft. 3 in. L. Baffle dimensions: 9 in. W x 3 ft. L. Inlets: (3) 2 in. S-line fittings, (1) 1 in. dia. S-line fittings, (1) 1/2 in. dia. port, (1) 2-1/2 in. dia. S-line fittings, (1) 2 in. dia. ports (jacket). Outlets: (1) 2 in. dia. S-line fittings, (2) 1 in. dia. FNPT fittings, (2) 2 in. dia. ports (jacket). Overall dimensions: 6 ft. 3 in. dia. x 8 ft. 8 in. H.



