

1996 Cherry-Burrell Superhomo Homogenizer

Mfg: Cherry-Burrell

Model: SS-7500-TGR

Stock No: WLDS153.100

Serial No: 184948 96

1996 Cherry-Burrell Superhomo Homogenizer. Model: SS-7500-TGR. S/N: 184948 96. Stainless steel clad homogenizer with a two stage remote hydraulic valve assembly and power unit. Maximum capacity: 3,000 GPH. Plunger size: 2.125 in. dia. Replaceable seat poppet valve cylinder. Maximum operating pressure: 4,500 psi. US electric motor, 150 hp, 1775 rpm, 460 V, 171 amps, 60 hz, 3 phase. Motor pulley diameter: 10- $\frac{1}{4}$ in. Gear pulley diameter: 21 in. Ratio: 2.0:1, final rpm: 875. Overall dimensions: 7 ft. 10 in. L x 4 ft. 2 in. W x 4 in. H. (ACN3900).





