

| FIG. & INDEX | ITEM NUMBER | DESCRIPTION                                            | QTY. | REV. | P & I REF. |
|--------------|-------------|--------------------------------------------------------|------|------|------------|
| 12—          | 720D0238    | Cycling Full-Lube Oil Pump, 480                        | Ref. | A    |            |
|              | 720D0047    | Full-Lube Oil Pump Piping, 60 & 76                     | Ref. | E    |            |
|              | 720D0228    | Full-Lube Oil Pump Piping, 100 & 134                   | Ref. | B    |            |
|              | 720D0085    | Full-Lube Oil Pump Piping, 177 & 222                   | Ref. | E    |            |
|              | 720D0073    | Full-Lube Oil Pump Piping, 270                         | Ref. | G    |            |
|              | 720D0106    | Full-Lube Oil Pump Piping, 316 & 399                   | Ref. | D    |            |
|              | 720D0237    | Full-Lube Oil Pump Piping, 480                         | Ref. | A    |            |
|              | 720D0119    | Oil Pump, 496 & 676                                    | Ref. | C    |            |
|              | 720D0211    | Full-Lube Oil Pump Piping, 856                         | Ref. | A    |            |
|              | 720D0048    | Full-Cycling Oil Pump, 60 & 76                         | Ref. | E    |            |
|              | 720D0229    | Full-Cycling Oil Pump, 100 & 134                       | Ref. | B    |            |
|              | 720D0086    | Full-Cycling Oil Pump, 177 & 222                       | Ref. |      |            |
|              | 720D0074    | Full-Cycling Oil Pump, 270                             | Ref. | E    |            |
|              | 720D0107    | Full-Cycling Oil Pump, 316 & 399                       | Ref. | D    |            |
|              | 720M0004G32 | Full-Cycling Oil Pump, 480, 60Hz                       | Ref. |      |            |
|              | 720M0004G31 | Full-Cycling Oil Pump, 480, 50Hz                       | Ref. |      |            |
|              | 720D0127    | Full-Cycling Oil Pump, 676                             | Ref. | C    |            |
| —1           | 950A0085G02 | Valve, Angle, Seal Cap, 1-1/2" Flg., 60—134            | 2    |      |            |
|              | 580D0019G02 | Valve, Angle, Seal Cap, 2" Flg., 177—222               | 2    |      |            |
|              | 950A0089H02 | Valve, Angle, Seal Cap, 2-1/2" Flg., 270—399           | 2    |      |            |
|              | 950A0137G02 | Valve, Angle, Seal Cap, 3" BW, 856                     | 2    |      |            |
| —2           | 954A0007H01 | Regulator, Differential Pressure, 1", 60—399           | 1    |      |            |
|              | 954A0007H06 | Flange Ring & Tube Assembly, 1"                        | 1    |      |            |
|              | 959A0057H03 | Gasket, Flange, 1"                                     | 2    |      |            |
|              | 954A0007H03 | Regulator, Differential Pressure, 1-1/4", 496—856      | 1    |      |            |
|              | 954A0007H07 | Flange Ring & Tube Assembly, 1-1/4"                    | 1    |      |            |
|              | 959A0057H04 | Gasket, Flange, 1-1/4"                                 | 2    |      |            |
| —3           | 956A0014H02 | Valve, Check, In-Line, 1", 60—399                      | 1    |      |            |
|              | 956A0014H01 | Valve, Check, In-Line, 1-1/4", 60—399                  | 1    |      |            |
|              | 956A0012G06 | Valve, Check, In-Line, 1-1/4", 496—856                 | 1    |      |            |
| —4           | 950A0069H07 | Strainer, 60 Mesh, 1-1/2", Current, (Hayward), 60—76   | 1    |      |            |
|              | 950A0069H25 | Gasket, Screen                                         | 1    |      |            |
|              | 950A0069H37 | Screen only                                            | 1    |      |            |
|              | 951A0037H16 | Strainer, 40 Mesh, 1-1/2", (Hubbel), 60—134            | 1    |      |            |
|              | 951A0037H26 | Screen only                                            | 1    |      |            |
|              | 951A0037H36 | Gasket, Screen                                         | 1    |      |            |
|              | 951A0037H14 | Strainer, 40 Mesh, 2", (Hubbel), 177 & 222             | 1    |      |            |
|              | 951A0037H24 | Screen only                                            | 1    |      |            |
|              | 951A0037H34 | Gasket, Screen                                         | 1    |      |            |
|              | 951A0037H15 | Strainer, 40 Mesh, 2-1/2", Original, (Hubbel), 270—399 | 1    |      |            |
|              | 951A0037H25 | Screen only                                            | 1    |      |            |
|              | 951A0037H35 | Gasket, Screen                                         | 1    |      |            |
|              | 950A0001H07 | Strainer, 60 Mesh, 2-1/2", Current, (R/S), 270—399     | 1    |      |            |
|              | 950A0001H26 | Kit, Screen (includes gasket & spring)                 | 1    |      |            |
|              | 950A0001H35 | Gasket, Flange                                         | 2    |      |            |
|              | 950A0001H09 | Strainer, 60 Mesh, 3", Current, (R/S), 496—856         | 1    |      |            |
|              | 950A0001H28 | Kit, Screen (includes screen, spring & gasket)         | 1    |      |            |
|              | 950A0001H36 | Gasket, Flange                                         | 2    |      |            |
| —5           | 960A0066G01 | Oil Pump/Motor, Viking, 1.5 HP, 1750 RPM               | 1    |      |            |
|              | 960A0066H01 | Pump, HJ495M                                           | 1    |      | P-1        |
|              | 960A0066H51 | Pump, Rebuilt, HJ495M                                  | 1    |      | P-1        |
|              | 960A0066H41 | Kit, Shaft Seal (incl. bearings, seal, o-ring & nut)   | 1    |      |            |
|              | 914A0015H02 | Motor only, 230/460V                                   | 1    |      | PM-1       |
|              | 960A0066H11 | Coupling, Drive                                        | 1    |      |            |