

Cherry Burrell, Ice cream freezer. Motor information has 3 motors unclose. 7-1/2 hp, 3 ph, and 50,60 cycles, frame: 254v, 208/220/440 volt. Amps: 22.3, 23.0, 21.0, 11.5, 10.5 rpm 1,500-1,800. SN-T16. Model 1039-00-166. All three motors have the same S/N and model no. It has 3 accumulators S/N CR7-191, F.P. no. 19968, S/N. CR7-194, S/N CR5868. It has 3 variable speed drivers. 1.2, 1.5 hp, 455/2,275 rpm, 230/460 volt, 4.75/2.32 amp, 60hz, S/N 850039259 all three are the same. 3 pulleys for barrels diameter is 14 in., barrel measurement 332 in. x 9 in. Barrel outlet is 1-1/2 in; it has 3 pumps on bottom with 1-1/2 in. outlet. It has a control switch panel with top barrel switch, pump switch, on side it has 3 pressure accurate switch, S/N C9612-0.



