

DTX BTX Model	Capacity BTUH/1°F TD				Air Data		Fans No./HP	Sound Level db(A)
	Wet		Frosted		CFM	Face FPM		
	DX	REC	DX	REC				
4-960	8760	10560	7970	9600	18400	620	(4) 1/3	73
4-1020	9310	11220	8470	10200	18000	606	(4) 1/3	73
4-1040	—	—	9630	10400	22000	741	(4) 1/2	75
4-1080	—	—	8960	10800	20000	673	(4) 1/2	75
4-1310	12100	14410	11000	13100	18280	615	(4) 1/2	75
4-1360	12570	14960	11425	13600	17240	580	(4) 1/2	75
4-1120	10230	12320	—	—	17200	579	(4) 1/2	75
5-1200	10960	13200	9960	12000	23000	618	(5) 1/3	74
5-1270	11640	14020	10580	12750	22500	605	(5) 1/3	74
5-1300	—	—	10790	13000	27500	739	(5) 1/2	76
5-1350	—	—	11200	13500	25000	672	(5) 1/2	76
5-1640	15150	18040	13775	16400	22850	614	(5) 1/2	76
5-1700	15700	18700	14280	17000	21550	579	(5) 1/2	76
5-1400	12780	15400	—	—	21500	578	(5) 1/2	76
6-1440	13150	15840	11950	14400	27600	619	(6) 1/3	75
6-1530	13970	16830	12700	15300	27000	605	(6) 1/3	75
6-1560	—	—	12950	15600	33000	740	(6) 1/2	77
6-1620	—	—	13450	16200	30000	673	(6) 1/2	77
6-1965	18160	21615	16510	19650	27420	615	(6) 1/2	77
6-2025	18710	22275	17010	20250	25860	580	(6) 1/2	77
6-1680	15340	18480	—	—	25800	578	(6) 1/2	77