

2002 Square D ISO-FLEX® Medium Voltage Controller

Mfg: Square D


Model: 4

Stock No: RBFM850A

Serial No:

2002 Square D ISO-FLEX® Medium Voltage Controller. Model: 4. Class E2, Factory Order No. 17-15018462-004, Category no. AG44D, 3 phase. Nominal system voltage: 4000 / 4160 V, rated maximum voltage 5kv, continuous current 360 amps, control voltage 120 vac volts. Impulse withstand: 60 Kv, Horizontal bus rating: 1200A. Power supply: Control voltage: 120 VAC, 60 Hz, 3 phase. Features include: front and rear access, and a NEMA 1 indoor, painted and gasketed enclosure. Inside enclosure dimensions: 5 ft. 11 in. L. x 2 ft. 7 in. W. x 8 ft. 3 in. H. Overall dimensions: 6 ft. L x 3 ft. W x 8 ft. 8 in. H. Run Hours: 10838.0(BG)(ACN303).





ISO-flex[®] MODEL 4
MEDIUM VOLTAGE
CONTROLLER CLASS E2

FACTORY ORDER NO. **17-15018462-004**
 CATALOG NO. **AG44D**
 MANUFACTURE DATE **2/02**
 RATED MAXIMUM VOLTAGE **KV 3**
 IMPULSE WITHSTAND (BIL) **KV 80**
 FREQUENCY **HZ 60**
 NUMBER OF PHASES **3**
 CONTINUOUS CURRENT **A 360**
 INTERRUPTING RATING **KA SYM 50**
 HORIZONTAL BUS RATING **A 200**
 POWER FUSE SIZE **5RT**
 CONTROL VOLTAGE **V 20VAC**

SQUARE D COMPANY
 DAYTONA, TN USA
 4630-021-01

Cutler-Hammer

CLS MOTOR CIRCUIT CURRENT LIMITING HIGH VOLTAGE FUSE

5ACL5-9R

5.09 MAX KV **RU**
 200(5R) AMP @
 50/60 HZ 151D933601
 MAX INT 60 KA SYN
 TWIN INT 740 AMP SYM

For Replacement Call 1-800-668-0888
Cutler-Hammer Inc.
 Pottsville, PA 17106
 www.clh.com/cutler-hammer.com

DO NOT modify or disassemble this device.
 Use only factory authorized replacement parts.
 DO NOT install or energize this device if it has been damaged. 4A35975H01

SQUARE D

TYPE SL50W430 MODEL C AC CONTACTOR

MAX CONT. AMPS	400	PHASES	3	BIL	60KV	CONTROL VA IN/USH	600 SEAL 30
MAX INT. CAPACITY	8500	A		CONTROL CIRCUIT VOLTS	120	AT HZ 60	
SYSTEM VOLTS	4160	DROPOUT TIME	130 mSEC	ALTITUDE		-1000m to +2000m	
C.O.	GS20348-01	COMPT.	4F	RU		N.P.7875440H01	

MADE IN U.S.A.

if it has been damaged. 4A35975H01

SQUARE D

TYPE SL50W430 MODEL C AC CONTACTOR

MAX CONT. AMPS	400	PHASES	3	BIL	60KV	CONTROL VA IN/USH	600 SEAL 30
MAX INT. CAPACITY	8500	A		CONTROL CIRCUIT VOLTS	120	AT HZ 60	
SYSTEM VOLTS	4160	DROPOUT TIME	250 mSEC	ALTITUDE		-1000m to +2000m	
C.O.	GS20348-02	COMPT.	5B	RU		N.P.7875440H01	

MADE IN U.S.A.

DO NOT modify or disassemble this device.
 Use only factory authorized replacement parts.
 DO NOT install or energize this device if it has been damaged. 4A35975H01

SQUARE D

TYPE SL50W230 MODEL C AC CONTACTOR

MAX CONT. AMPS	200	PHASES	3	BIL	60KV	CONTROL VA IN/USH	600 SEAL 30
MAX INT. CAPACITY	8500	A		CONTROL CIRCUIT VOLTS	120	AT HZ 60	
SYSTEM VOLTS	4160	DROPOUT TIME	250 mSEC	ALTITUDE		-1000m to +2000m	
C.O.	GS20348-02	COMPT.	3D	RU		N.P.7875440H01	

MADE IN U.S.A.