

Vilter VRS-900B / WRV204/1.65 Howden Rotary Screw Compressor Package – 125 HP

Mfg: Vilter Howden

Model: VRS-900B/WRV204/1.65

Stock No: DWKN4004

Serial No: MK4B/WRV204/16526

Vilter VRS-900B / WRV204/1.65 Howden Rotary Screw Compressor Package. Model: VRS-900B/WRV204/1.65. S/N: MK4B/WRV204/16526. Contract No: JH0741. Capacity rating: 308 tons at 357 BHP using R-717(ammonia) with suction temperature of 20°F / 33.5 psig and condensing temperature of 95°F and 181 psig. Displacement: 853 cfm. Electric motor: Estimated shipping weight: 7100 lbs. Total hours on compressor: 91,460. Overall dimensions: 13 ft. 2 in. L x 4 ft. 8 in. W x 8 ft. 6 in. H.







