

565 Gallon Processor, split lift covers, painted exterior, motor less motor plate, less jacket rating, 2 - 1/2 in stainless steel valved outlet, 3 in Jacket side outlet, thermal probe, 2 in and 3 in top inlet on bridge, 60 in wide-sweep agitator with vertical baffle, inner dimensions 66 in. diameter x 39 in. H, Overall dimensions 79 in. L x 79 in. W x 70 in. H.

