




CATALOG NUMBER*	ACCUM. CAP (TONS)	SYSTEM CAPACITY (GPM)	DUMP TRAP DIA x LNG (IN.)	"X" (MIN REQ'D, IN.)		"Y" (REF.) (IN.)	IPS LINE SIZES				SHIPPING WEIGHT (LBS.)
				VERT.	HOR.		L1 VENT	L2 GAS	L3 TRANSFER	L4 DRAIN	
T187V/H**	140	3.7	12 x 26	30	25	10	3/4	3/4	3/4	1 1/4	270
T287V/H	240	6.1	12 x 26	30	25	10	3/4	3/4	3/4	1 1/2	285
T387V/H	440	10.9	16 x 38	40	30	11	3/4	3/4	1 1/4	2	430
T487V/H	760	19.1	20 x 40	46	35	13	1 1/4	1 1/4	1 1/4	3	670
T587V/H	1480	31.2	24 x 42	47	42	16	1 1/4	1 1/4	2	4	810
T687H	2000	56.5	24 x 72	SP.	42	16	1 1/4	1 1/4	3	4	1180
T787H	3000	73.4	24 x 84	SP.	42	16	2	1 1/4	3	4 (2)	1630

Ordering Instructions:

* When ordering, specify suffix "V" (for vertical dump trap) or suffix "H" (for horizontal dump trap).

** Do not use 187 size systems when accumulator suction temperature is below 0°F. Upsize to 287 system.