

Stainless Steel Jacketed Processing Tank-150 Gallon

Mfg:

Model:

Stock No. tAFP001.

Serial No.:

Stainless Steel Jacketed Processing Tank-150 Gallon. Cone bottom. Inside dimensions (straight wall): 30-1/2 in. dia. x 47 in. H. Side-scrape agitator: 26-1/2 in. W x 46 in. H. Agitator has (12) 12 in. L blades and (10) 7-1/2 in. intermediate blades. Its (3) 34 in. long legs are attached to a 48 in. L x 37-1/2 in. W x 12 in. H base with casters for easy maneuverability. Sew-Eurodrive Motor, 1.5 hp, 1700 rpm, 230/460 V, 4.75/2.35 amps, 60 Hz, 3 phase. Sew-Euro Variable Speed Drive Module, Rpm Input: 453-2264, Rpm Output: 1600-7800, Torque: 980. Inlets: (1) 2-1/2 in. male pipe threaded port. Outlet: (1) 3 in. male pipe threaded port. Inlet/Outlet for heat supply: (2) 3 in. female pipe thread ports. Overall dimensions: 66 in. L x 38 in. W x 107 in. H.



