



NOTE: THE QUANTITY OF FANS, FAN MOTORS AND LUBE FITTINGS ARE IDENTICAL ON BOTH SIDES

TAG SHIPMENT: PO# 14894

ADD CATWALK/HANDRAIL WEIGHT: 3505 LBS. (LADDER(S) INCLUDED) TO OPERATING WEIGHT ON FOUNDATION DRAWING	MAX. CONCENTRATED CATWALK LOAD WEIGHT: 300 LBS./LINEAR FT.	COIL TO BE NITROGEN CHARGED WITH 25 PSIG BEFORE SHIPMENT.
	MAX UNIFORM CATWALK LOAD WEIGHT: 1000 LBS./LONG OR SHORT SIDE	

INCLUDED OPTIONS: .060" TUBE COIL; OVERSIZED HINGED ACCESS DOOR; INDIVIDUAL FAN DRIVES & PARTITIONS; PREM EFFCY RELIANCE FAN MOTORS; PRESSURE GAUGES MOUNTED ON EACH FLANGED WATER SPRAY INLET CONNECTIONS; SERVICE PLATFORM W/LADDER & CAGE

STANDARD UNIT DATA:
 CASING: HDG AFTER FAB
 REMOTE: 1200 GPM @ 2.0 PSI
 FAN MOTOR: (4) 5 HP TE 1800 RPM
 200/208-3-60 184T FRAME E+
 FOUNDATION LAYOUT: 420022B

PERFORMANCE DATA:
 8442.6 MBH THR @ 78F WB
 95F COND
 R-717; 0" ESP
 COIL VOLUME: 131.84 CU. FT.
 DESIGN PRESSURE 300 PSI

LTR	DESCRIPTION	DATE	BY
A	REVISED FAN VOLTAGE FROM 460	3/28/06	JRS

Frigid Coil/Imeco
 YORK INTERNATIONAL

*** NOTE: Cut these ratings in half for a single tower (XLP-XL-425)**

MODEL: XLP XL-850-2
 EVAP. CONDENSER
 DRAWING NO. 477500100

1/1