

Baldor Electric Motor - 500 HP

Mfg: Baldor

Model:

Stock No. DTTC819B.

Serial No. N071/0174-01081612

Baldor Electric Motor - 500 HP. Specification Number 20E009-0330. S/N: N071/0174-01081612. Motor specifications: 3580 rpm, 2300/4160 V, 109/61 amps, 60 Hz, 3 phase. Continuous duty. Enclosure: WP11. Frame: 5009Z. Insulation class: F. NEMA code: F. Weight: 6000. Overall dimensions: 4 ft. 4 in. L x 4 ft. W x 4 ft. 4 in. H.

