

## Hobart 4146 Meat Grinder

Mfg: Hobart

Model: 4146

Stock No: EELD568.3a

Serial No: 11-033-304

Hobart Meat Grinder. Model: 4146. S/N: 11-033-304. ML: 16812. Nominal fresh beef capacity: 50 pounds of beef per minute. Screw Auger dimensions: 13 in. L x 3-1/4 in. dia. Pitch: 1-1/2 in. MAWT: 500 °F. Electric Motor, 5 hp, 1725 rpm, 208 V, 20.6 amps, 60 Hz, 3 phase. Suitable for fresh or tempered frozen meat (above 26°F), this grinder is designed for fast, clean cutting of meat where high-quality ground products are of prime importance. Standard equipment consists of a working power unit with magnetic-type starter and push buttons completely wired to motor, waterproof junction box on rear of machine requiring only power connection, Hobart grinding end and high back, large-capacity tinned feed pan with guard. Inlet: (1) 4 in. W x 6 in. L. (top infeed). Outlet: (1) 3-1/2 in. dia. port. Overall dimensions: 4 ft. 9 in. L x 1 ft. 6 in. W x 3 ft. 2 in. H.





