

Vulcan-Hart Direct Steam Fully Jacketed Kettle- 150 Gallon

Mfg: Vulcan-Hart

Model: ST150

Stock No. EECS017.2

Serial No. 14305

Vulcan-Hart Direct Steam Fully-Jacketed Kettle-150 Gallon. Model: ST150. S/N: 14305. Stainless steel. Inside dimensions: 33-1/2 in. dia. x 42-1/2 in. H (at deepest point). Sloped bottom for easy product flow. Steam flow rate @ 15 psig: 269 lbs/hr for fast boil, 215 lbs/hr for medium boil, 165 lbs/hr for slow boil. Kettle features electrically operated temperature controls for steam cut in/out, a temperature probe, and a pressure regulator. Electrical requirements: 120 V, 0.5 amps. Inlets: (1) 3/4 in. dia. FPT for jacket. Outlets: (1) 3/4 in. dia. FPT for jacket, (1) 2 in. dia. FPT for kettle. Overall dimensions: 56 in. L x 42 in. W x 57 in. H.

