

## FMC 100 Paddle Pulper / Finisher Stainless Steel

Mfg: FMC

Model: 100

Stock No. 125.L63001.8a

Serial No. CM 1634

FMC Paddle Pulper/Finisher. Model: 100, S/N: CM 1634. Cylindrical screen chamber: 18 in. dia x 36 in. L. (4) paddles. Product intake: 4 in. dia. Liquid outlet: 2 1/2 in. Pomace outlet: 9 in. L x 5 in. H. US motor: 20 hp, 220/440 V, 52/26 amps, 60 Hz, 3 phase. Final speed: Approx. 808 rpm. The FMC Pulper/Finisher reduces tomatoes, fruits and vegetables to a semi-liquid or liquid state. It eliminates pits from stoned fruit pulp and separates seeds, skins, and extraneous particulate materials from pureed pulp. Overall dimensions: 97 in. L x 43 in. W x 54 in. H.



