

Resina Capper

Mfg: Resina

Model: S-30

Stock No. 75.IMS1a

Serial No. 81 6155

Resina Capper. Model: S-30. S/N: 81 6155. Max. Cap dimensions: 2 in. dia. x 3/4 in. H (50.80 mm dia. x 19.05 mm H). Last used with 1-1/2 in. W x 1/2 in. H caps (38.10mm dia. x 12.70mm H). Productivity: 24/60 per minute (glass and metal containers), 24/55 per minute (plastic containers). Single head unit. Conveyor belt maximum width: 4 in. Conveyor belt length: 83 in. General Electric Motor, 1 hp, 1725 rpm, 115/230 V, 13.2/6.6 amps, 60 Hz, single phase. Speed reducer, 30 ratio, 998 in. lb of torque, 57.5 final rpm. Cap sorter is belt driven with a Boston speed reducer. General Electric Motor: 1/3 hp, 1725 rpm, 115/230 V, 6.0/3.0 amps, 60 Hz, single phase. Inlets/exit height: 34 in. Overall dimensions: 83 in. L x 47 in. W x 94 in. H.



