

## Copeland Air Cooled Condensing Unit

Mfg: Copeland

Model:

Stock No. MHCR306.1a

Serial No.:

Copeland Air Cooled Condensing Unit. Copeland Scroll Compressor, Model: G155ET-017, S/N: G0090E076006AG4534A, power supply: 230-208/220-200 V, 60/50 Hz. Condenser fins per inch: 11. Number of fans: 2. Fan diameter: 1 ft. 1 in. Mars Fan Motor, 1/10 hp, 1550 rpm, 115/230 V, 5.0/2.5 amps, 60 Hz, single phase. Emerson Fan Motor, 1/10 hp, 1550 rpm, 115/208 V, 3.8/1.9 amps, 60 Hz, single phase. Accumulator- 1 Gallon, inside straight-wall dimensions: 5 in. dia. x 1 ft. H. Refrigerant Receiver- 1.5 Gallon, inside straight-wall dimensions: 6 in. dia. x 1 ft. 1 in. H. Sporlan Valve Company Filter Dryer, Model: C-163S, refrigerants: R12, R134a, R22, R404a, R407c, R410a, R500, R502, R507. Inlets: 1 in. dia. port. Outlets: 1/16 in. dia. port. Overall dimensions: 2 ft. 11 in. L x 2 ft. 2 in. W x 1 ft. 11 in. H.





