

Hi-Speed Checkmate Checkweigher with Conveyor


Mfg: Hi-Speed



Model: CM

Stock No. HDFD361.17

Serial No. CM-11428

Hi-Speed Checkmate Checkweigher with Conveyor. Model: CM. S/N: CM-11428. Wiring Diagram: D2-81-147. Power supply: 115 V, 1.0 amps, 60 Hz, single phase. Hi-Speed Conveyor. Model: CM65SH CM. S/N: 11428. Job No. 940072. Conveyor belt dimensions: 4 ft. 11 in. L x 1 ft. 1 in. W. Infeed/exit height: 3 ft. 3 in. Pneumatic reject mechanism dimensions: (2) 7-1/2 in. L x 2 in. W. Belt motor, 1/2 hp, 1725 rpm, 208-230/460 V, 2.2-2.2/1.1 amps, 60 Hz, 3 phase. Adjustable operator touchpad control panel. Overall dimensions: 5 ft. L x 3 ft. 1 in. W x 5 ft. 4 in. H.





HI-SPEED
HI-SPEED CHECKWEIGHER CO., INC.
ITHACA, NY 14850
ENCLOSED INDUSTRIAL CONTROL PANEL
MODEL # _____ SERIAL # 00-11328
THIS EQUIPMENT IS DESIGNED TO THE
FOLLOWING ELECTRICAL SPECIFICATIONS:
SUPPLY: _____ VOLTS _____ PHASE
OVER CURRENT PROTECTION PROVIDED AT _____ AMPS
WIRING DIAGRAM _____ TERMINALS PROVIDED AT _____
LARGEST _____