

## FMC 200 Pulper/Finisher

Mfg: FMC

Model: 200

Stock No. SGMPB141.87a

Serial No. 4701-54-83

FMC 200 Pulper/Finisher. Model: 200. S/N: 4701-54-83. Screen size: 0.020 in. mesh. (4) Beater blades: 34 in. L x 2-1/2 in. W. Baldor Industrial Motor, 20 hp, 1160 rpm, 870 rpm (final), 230-460 V, 54-27 amps, 60 Hz, 3 phase. Inlets: (1) 4 in. dia. I-line fitting (infeed). Outlets: (1) 2-1/2 in. dia. I-line fitting (liquid), (1) 8-1/2 in. x 4-1/2 in. pulp exit door with spring return (pulp); door has (5) tension settings and flows into (1) 24 in. L x 4 in. W discharge chute. Overall dimensions: 54 in. L x 43-1/2 in. W x 49 in. H. (ACN440)  
The FMC FoodTech Pulper/Finisher reduces tomatoes, fruits and vegetables to a semi-liquid or liquid state. Product is dispersed by a circular distributor and then pressed against a mesh screen by beater blades. It eliminates pits from stoned fruit pulp and separates seeds, skins, and extraneous particulate materials from pureed pulp. A specialty use for it is in baby food. In this case, it reduces the size of preheated pureed vegetables used in baby foods. Alternative uses include mixing and blending ingredients during the finishing operation. These results in higher yield, increased capacity, improved quality of finished products, and longer screen life.





