

## FMC Model 100 Pulper Finisher

**Mfg: FMC Technologies**

**Model: 100**

**Stock No.: TAFM305.7**

**Serial No.: AN-1512**

FMC Paddle Pulper/Finisher. Model: 100. S/N: AN-1512. Stainless steel frame. Number of paddles: 4. Paddle dimensions: 3 ft. 10 in. L x 2 in. W. Baldor motor, 15 hp, 1760 rpm, 208-230 V, 41-38/19 amps, 60 Hz, 3 phase. Driver pulley dia.: 5-7/8. Driven pulley dia.: 15-3/4. Ratio: 2.7. Final rpm: 652. Inlets: (1) 4 in. dia. port. Outlets: (1) 4 in. dia. port with S-line Fitting. (1) 5 in. L x 3 in. W. (product discharge). Overall dimensions: 7 ft. 2 in. L x 3 ft. 4 in. W x 3 ft. 9 in. H.









