

1997 Jordan Ammonia Recirculator Package – 48 in. Dia. x 10 ft. 1 in. L

Mfg: Jordan Equipment Sales

Model: HR 48-148

Stock No: KWBF003

Serial No: 97-2584

1997 Jordan Equipment Sales Ammonia Recirculator Package. Model: HR 48-148. Refrigerant: R-717 (Ammonia). Approximate capacity: 1,050 gallons. MAWP: 250 psi @ 200°F. MDMT: -20°F @ 250 psi. Radius: 2:1 elliptical ends. (2) 1997 Cornell refrigerant pumps. Model: 2CB-5-4. Flow rate for new pump is 117 gpm with required horsepower and pressure. Baldor electric pump motor, 5 hp, 1760 rpm, 230/460 V, 13.6/6.8 amps, 3 phase. Jordan Equipment Sales oil pot. Model: HOP 10-36. MAWP: 300 psi @ 200 °F. MDMT: -20 °F @ 300 psi. Inlets: (1) 8 in. dia. port, (2) 2 in. dia. port, (1) 1 1/2 in. dia. port. Outlets: (1) 8 in. dia. port, (2) 6 in. dia. port, (1) 1 1/2 in. dia. port, (3) 1 in. dia. port. Overall dimensions: 13 ft. 2-1/2 in. L x 6 ft. 7 in. W x 14 ft. 8 in. H.







