

Cast Screw Auger Grinder with Stainless Frame – 5 in. dia.

Mfg: Not Specified

Model:

Stock No: TAFM500.1

Serial No:

Screw Auger Grinder. Auger dimensions: 5 in. dia. x 1 ft. 9 in. L. Pitch: 3 in. Leeson electric motor, 5 hp, 1750 rpm, 208-230/460 V, 14.2-13.8/6.9 amps, 60 Hz, 3 phase. Inlets: (1) 6-1/4 in. L x 6-1/4 in. W (infeed). Outlets: (1) 3 in. dia. S-line fittings. Overall dimensions: 4 ft. 5 in. L x 2 ft. 5 in. W x 2 ft. 5 in. H.





LEESON		IMB	
CAT. NO.		VOLT.	
MODEL		AMP.	
R.P.M.	S.F.A.	FR.	HZ.
EFF.	100% FL	EFF.	75% FL
F.F.	MAX. AMB.	°C INS. CL.	
C/DOE		DATE	
SER.3		ENCL.	
LEESON ELECTRIC CORPORATION			