

FOGG 15-Valve Rotary Filler

Mfg: FOGG

Model: Fed G15 LH

Stock No. WHFD01.35

Serial No. 5566-9-82

FOGG 15-Valve Rotary Filler. Model: Fed G15 LH. S/N: 5566-9-82. Filler capacity: ½ gallon jugs. (15) Valves: 1-1/8 in. diameter x 6 in H; center to center: 7-3/4 in. Base dimensions: 6 in. L x 5 in. W. Space from base to valve: maximum (open) 12-1/2 in. minimum (close) 9 in. Tank capacity: 50 gallons; top manway: 15-1/2 in. diameter. Tel-Tru temperature gauge in tank (20°F to 240°F). Change parts dimensions for jug cross-over: 13 in. diameter. Clearance: 6 in. L x 5 in. Float activated product infeed. CIP system. Conveyor dimensions: 70 in. L x 6 in. W. Baldor Motor, ½ hp, 1140 rpm, 208-230/460 V, 2.5-2.4/1.2 amps, 60 Hz, 3 phase. Inlet opening for tank: 6 in. diameter. Valve opening for tank cleaning: ½ in. threaded female. Overall dimensions: 78 in. L x 72 in. W x 80 in. H.





