

Azo Solid/Liquid Screener


Mfg: Azo

Model: FLF-650

Stock No. NPPC202.a

Serial No. 12082

Azo Solid/Liquid Screener. Model FLF-650, S/N 12082. Stainless steel. Inlets/outlets: (2) 2 in. Q-line, (1) 4 in. Product Chamber: 13-1/2 in. dia x 32 in. L. Rectangular exit aperture: 5 in. x 6 in. Hinged lid aperture: 5 1/2 in. x 18 in. Simple dismantling with quick release clamps. SEW Varidrive motor: 2 hp, 1720 rpm, 230/460 V, 6/3 amps, 60 Hz, 3 phase. SEW reducer: ratio: 2.48, torque: 119 lb in., input speed: 460 - 2290 rpm, output speed: 185-928 rpm. Overall dimensions: 82 in. L x 30 in. W x 52 in. H. This screener is designed for continuous separation of solids from liquids. Examples include: Fruit pulp from fruit juice, butter from buttermilk, cheese fines from whey.



For additional information click the links.

[NPPC202screener1.pdf](#)

[NPPC202screener2.pdf](#)

[NPPC202screener3.pdf](#)

