

APV HTST Press- 5,000 GPH


Mfg: APV

Model:

Stock No.: pHDMD300.73a

Serial No.:



APV HTST Press- 5,000 GPH. APV Crepaco Plate Heat Exchanger, Model R51, S/N 17064. (238) Diagonal flow plates. Surface heating area: 1198 sq. ft. (2) Dividers. (2) Pumps - (1) Fristam, (1) APV. Holding tube: 23 gallons. Balance tank: 152 gallon. Maximum aperture: 83 in. L. Inlets/outlets: (4) 3 in. "S" line, Inlets/outlets from dividers: (2) 2-1/2 in. "S" line. Overall dimensions: 145 in. L x 36 in. W x 95 in. H.



APV Crepaco Sanitary Centrifugal Pump. Model: 8V. S/N: D-7401. Impeller diameter: 7-1/2 in. Single mechanical seals and Water flush. Reliance Electric Motor, 5 hp, 1745 rpm, 230/460 V, 12.4/6.2 amps, 60 Hz, 3 phase. Inlets: (1) 3-1/2 in. threaded male. Outlets: (1) 2 in. threaded male. Overall dimensions: 24 in. L x 14-1/2 in. W x 16 in. H.



Fristam Centrifugal Pump. Model: FPX3541-205. S/N: 354172305. Impeller diameter: 6 in. Single mechanical seals. Baldor motor, 10 hp, 3450 rpm, 208-250/460 V, 25-24/12 amps, 60 Hz, 3 phase. Inlets: (1) 3 in. threaded male. Outlets: (1) 1-1/2 in. threaded male. Overall dimensions: 26 in. L x 17-1/2 in. W x 16 in. H.



Holding tube. Maximum capacity in the tube: 23 gallons. Inlets/Outlets: (2) 3 in. threaded male, 3 in. "S" line. Overall dimensions: 110 in. L x 32 in. W x 82 in. H.



Balance Tank. Capacity: 152 gallons (48 in. L x 35 in. W x 21 in. H). Inlets/outlets from well: (2) 4 in. "S" line, 3-1/2 in. threaded male, 3 in. threaded male, 3-1/2 in. threaded male discharge. Inlets/Outlets from the top: 3-1/2 in. "S" line, 3 in. "S" line, 3 in. threaded male, 2-1/2 in. threaded male, 2 in. threaded male, (2) 4 in. pipes. Overall dimensions: 48 in. L x 36 in. W x 36 in. H.

