

1992 M&M Refrigeration Ammonia Recirculator- 6 ft. dia. x 10 ft. L

Mfg: M&M Refrigeration


Model:

Stock No. sEELD665A.1a

Serial No. 92A038

1992 M&M Refrigeration Ammonia Recirculator- 6 ft. dia. x 10 ft. L. S/N: 92A038. Nat'l Bd: 243. MAWP: 250 psig @ 650°F. MDMT: 250 psig @ -50°F. (2) Cornell Centrifugal Pumps, Model No: 2CB-3-4, S/N's: 64342 and 67713. (2) Marathon Electric Motors, 3 hp, 1735 rpm, 230/460 V, 8.6/4.3 amps, 60 Hz, 3 phase. Inlets: (1) 10 in. dia. port, (1) 8 in. dia. port, (1) 1 in. dia. FNPT fitting, (1) 1-1/2 in. dia. port, (1) 2 in. dia. port. Outlets: (2) 3 in. dia. ports, (2) 1 in. dia. FNPT fittings, (2) 1-3/4 in. dia. ports, (2) 3/4 in. dia. ports. Overall dimensions: 12 ft. L x 6 ft. 7 in. W x 8 ft. 11 in. H.







1992 M & M Oil Pot- 10 Gallon. S/N: 230. Straight-wall dimensions: 10 in. dia. x 2 ft. 6 in. L. MAWP: 500 psig @ 650°F, MDMT: 300 psig @ -50°F. (2) Hansen Technologies Pressure Relief Valves, S/N: 01B, Cat. No: H5600R, capacity: 226 scfm, max pressure: 250 psi. Inlets: (1) 3/4 in. dia. port, (1) 2 in. dia. port. Outlets: (1) 3/4 in. dia. port, (1) 1 in. dia. FNPT fitting. Overall dimensions: 3 ft. 5 in. L x 1 ft. 8 in. W x 3 ft. 2 in. H.

