

Mycom 8-Cylinder Reciprocating Ammonia Compressor Package-125 HP

Mfg: Mycom

Model: N8B

Stock No: tMMO005B

Serial No: 10804

Mycom 8-Cylinder Reciprocating Ammonia Compressor Package -125 HP. Model: N8B. S/N: 10804. Leak test pressure hi/lo: 313-185 psig. Hydrostatic pressure hi/lo: 470-470 psig. Max speed: 1,200 rpm. Bore: 5-1/8 in. Stroke: 3-15/16 in. Lincoln electric motor, 125 hp, 1770 rpm, 230/460 V, 288-144 amps, 60 Hz, 3 phase. Reco oil separator, S/N: W800-1-1, Nat'l Bd: 2890, MAWP: 250 psi @ 300 °F, shell thk: 0.375 in., head thk: 0.375 in. Reco receiver tank, S/N: S-1403-1-5, Nat'l Bd: 2764, MAWP: 300 psi @ 650 °F, shell thk: 0.250 in., head thk: 0.250 in. Klockner Moeller Corp. control starter box, Series: 200, electrical requirements: 460 V, 600 amps (main bus), 300 amps (vert bus), 300 amps (ground bus), 3 phase. Inlets: (1) 2 in. dia. suction pipe with a 4-1/2 in. L x 4-1/2 in. W flange & (4) 1/2 in. dia. attachment holes at a center-to-center distance of 3 in. Outlets: (1) 4 in. dia. discharge pipe with a 7 in. L x 7 in. W flange and (4) 1 in. dia. attachment holes at a center-to-center distance of 5 in. Overall dimensions: 15 ft. 8 in L x 8 ft. 8 in. W x 10 ft. H.





