

FMC Technologies (JBT FoodTech) Stainless Steel Screw Finisher

Mfg: FMC Technologies (JBT FoodTech)

Model: UCF200A

Stock No: RCJF682.35

Serial No: 8332

FMC Technologies (JBT FoodTech) Stainless Steel Screw Finisher. S/N: 8332. Capacity range: 20 to 60 tons per hour. Pulley dia. driver 7-1/4 in. driven 25-5/8 in. This unit has capabilities for a full range of fruit and vegetable reduction, including oil finishing (separating frit from the oil water emulsion), recovery of soluble solids (pulp wash), core wash eliminating pits from stoned fruit pulp, separates seeds, skins and extraneous particulate materials from pureed pulp. Alternative uses include mixing and blending ingredients during the finishing process. Speed of drive shaft: 780 rpm. All components are made of stainless steel or other corrosion resistant materials. Drive motor: 30 hp. (1) S-Line inlet: 4 in. (2) Acme outlets 4 in. Overall dimensions: L. 5ft. 10-1/4 in. X W. 2ft. 7-1/2 in. X H. 4ft. 2-5/8 in. (ACN967A-83).







