

Armstrong Steam Trap Set

Mfg: Armstrong

Model: PT308-1

Stock No. SPGP014.a

Serial No. 6683

Armstrong Steam Trap Set. Model: PT308-1. S/N 6683. Max. operating pressure: 125 psi. MAWP: 150 psi @ 425 °F. (2) 1999 Armstrong fluid handling tanks, Model: 1627-1446, Nat'l Bd: 315959. Certified LaGrange Product Fremont. MAWP: 150 psi @ 650 °F, MDMT: -20 °F @ 150 psi. (3) Globe valves. Inlets: 1 in. dia. port, 1/2 in. dia. NPT port (male), 1-1/2 in. dia. NPT port (male). Outlets: 1-1/2 in. dia. port, 1/2 in. dia. NPT port (male), 2 in. dia. port. Overall dimensions: 61 in. L x 37 in. W x 40 in. H.

