

1990 Precision Heat Exchanger Co. Products Chiller with Surge Drum – 256 Sq. Ft.

Mfg: Precision Heat Exchanger Co.

Model:

Stock No: AACA2074A.5

Serial No: 11870-3 & 11870-4

1990 Precision Heat Exchanger Co. Products Chiller with Surge Drum. Serial number: 11870-3 & 11870-4. Nat'l Board no(s). 5278 & 5279. Estimated maximum capacity of heat exchange surface area: 256 sq. ft. (54) 1 in. diameter x 217 in. L carbon steel tubes. Shell side MAWP: 250 psi @ 200°F, MDMT: -20°F @ 250 psi. Tube side: MAWP: 100 psi @ 200°F, MDMT: -20°F @ 100 psi. (3) Henry Valve Co. model: LI-50 liquid level indicators. (2) Parker safety relief valves. Type SRH204. Set pressure: 250 psig. Air capacity 747 scfm. (2) WIKA dial temperature gauges. (2) Parker type LL, float switch assemblies. Inlet / outlets: 5 in. Overall dimensions: 19 ft. 6 in. L x 2 ft. 5 in. W x 4 ft. 9 in. H.



