

## Urschel Dicer, Model G-A

Mfg: Urschel

Model: G-A

Stock No. ANSA002.

Serial No. 3291

Urschel Dicer. Model G-A, S/N 3291. U.S. Motor: 2 hp, 1,730 rpm, 6.0/3.0 amps, 60 Hz, 3 phase. Crosscut knife cut sizes: 1/2 in. Circular knife cut sizes: 3/4 in. Slice thickness range: 1/8 in. to 5/8 in. Urschel Model G-A uniformly cuts dices, straight french fry strips, and slices from a variety of soft ripe fruits and brittle root vegetables. A wide selection of interchangeable cutting parts enables the user to obtain gentle, clean cutting through a wide range of sizes at high production capacities. The Model G-A features continuous operation for uninterrupted production, and simplified design for easy cleanup and maintenance. Maximum input product size is 5-1/2 in. (139.7 mm) in any dimension. Overall dimensions: 60 in. L x 29 in. W x 50 in. H. Types of Cuts- SLICES: By removing the crosscut knife spindle, the circular knife spindle, and the stripper plate, the Model G-A can make slices up to 3/4 in. (19.1 mm) with the addition of optional parts.

DICES: A slicing knife, crosscut knife spindle, and circular knife spindle are used for dicing. Changing the size of the cubes is done by using the required cutting spindles and adjusting the slice thickness. Cubes up to 3/4 in. (19.1 mm) may be obtained. STRIP CUTS: To make strip cuts, only the slicing knife and the crosscut knife spindle are used. Strip cuts up to 17/32 in. (13.5 mm) may be obtained. JULIENNE STRIPS: Julienne strips are also available.





