

FMC Paddle Pulper / Finisher

Mfg: FMC

Model: 100

Stock No. tPB001.

Serial No.

FMC Paddle Pulper / Finisher. Model: 100. Paddle dimensions: (4) 34 in. L x 2 ½ in. Reliance Electric Motor, 20 hp, 1,760 rpm, 460 V, 24 Amps, 60 Hz, 3 phase. Drive, ratio: 2.5, 704 rpm out (final). The FMC 100 Pulper / Finisher reduce tomatoes, fruits, and vegetables to a semi-liquid or liquid state. It eliminates pits from stoned fruit pulp and separates seeds, skins, and extraneous particulate materials from pureed pulp. Inlet: (1) 4 in. dia. ACME fittings. Outlet: (1) 4 in. dia. ACME fittings. Product discharge: 8 ½ in. L x 4 ½ in. W. Overall dimensions: 8 ft. 4 in. L x 3 ft. 4 in. W x 6 ft. 2 in. H.





