

## Baltimore Aircoil Company Evaporative Condenser – 52 Tons

Mfg: Baltimore Aircoil Company


Model: C1722HR

Stock No: AAEC840F

Serial No: 88600427

Baltimore Aircoil Company Evaporative Condenser. Model: C1722HR. S/N: 88600427. Belt No: B68. Refrigerant: R-22. Nominal capacity rating using Freon: 52 tons at 105°F condensing, 40°F suction, and 78°F wet bulb temperatures, or approximately 37 tons when used with ammonia (R-717) at 96.3°F condensing, 20°F suction and 78°F wet bulb temperatures. U.S. Electrical Motor, 5 hp, 1720 rpm, 34 rpm (final), 230/460 V, 13.4/6.7 amps, 60 Hz, 3 phase. Manway equipped. 13 in. dia. centrifugal fans. Inlets: (1) 2 in. dia. media port. Outlets: (1) 2 in. dia. media port, (1) 3 in. dia. port. Approximate shipping weight: 2590 lbs. Overall dimensions: 6 ft. 10 in. L x 4 ft. W x 8 ft. 2 in. H.(ACN109-88).









**Baltimore Aircoilt  
Company, Inc.** P.O. BOX 7  
PAXTON, IL. 60957  
(217) 379-2311

MODEL NO. C1722HR  
SERIAL NO. 88600427  
BELT NO. B68

**B.A.C.**

SUBSIDIARY OF AIRBEC & CO., INC. PN 27-178-PA REV. A

**BALL BEARING  
LUBRICATION INSTRUCTIONS**